

DATA SHEET

**AO-Y-1573**/1~30uJ/1~1000mW

## LD PUMPED ALL-SOLID-STATE **AOM Q-SWITCHED LASER**

All solid state AOM Q-switched laser at 1573 nm has the features of high peak power, high repetition rate, and short pulse duration, which is widely used in laser radar ranging, spectrometry, remote sensing, and so on.









## SPECIFICATIONS

| 1573±3                   |
|--------------------------|
| Acousto-Optic Q-switched |
| 1~1000@30kHz             |
| ~11@30kHz&1000mW         |
| 5~50                     |
| 1~30                     |
| 1~3000                   |
| <2%, <3%                 |
| <4                       |
| ~7                       |
| 88                       |
| <10                      |
| 15~35                    |
| PSU-AOM (3U)             |
| 10000                    |
| 1 year                   |
|                          |





