

Beam Profiler



Features:

Spectral range: 340-1100nm

Beam diameter: 17 μ m~4.5mm

Maximum power to 1W

PC software

SPECIFICATIONS

Product Name	CN0104VIS-B
Spectral Range	340-1100nm
Sensor Size	6.4mm*4.5mm
Resolution	3840*2748
Dynamic Range	54dB
Pixel Size	1.67 μ m
Exposure Time	0.162ms~500ms
Shutter Type	Rolling Shutter
Beam Diameter	17 μ m~4.5mm
Maximum Power Density	50W/cm ² (OD3.5)
Maximum Power	1W
Attenuator	general band: OD0.5/OD1/OD2/OD3 (340-1100nm)
Communication Interface	GigE
Full Resolution Frame Rate	5-10fps ^①
External Triggering	Not available
Dimensions	Reference structure diagram
Operating Environment	Temperature < 0~35 $^{\circ}$ C ^② ; Relative humidity < 60%; Pointing test temperature: 15-25 $^{\circ}$ C
Operating System	Windows 10/11, 64-bit, pre-installed MS Office or WPS Hardware configuration: \geq 8G memory, CPU frequency \geq 2.5G, core \geq 4, i5 and above are recommended, and the best display resolution is 1920*1080
Weight	< 500g
Warranty	1 year

Note: 1. This parameter refers to the frame rate at 5 million pixels.

2. This is the operating temperature, if it involves directivity test, the temperature should be controlled at 15-25 $^{\circ}$ C.



CN0104VIS-B

