



Beam Profiler



Features:

Spectral range:532nm
Beam diameter:2 μ m~250 μ m
Maximum power to 5W
PC software

SPECIFICATIONS:

Product Name	CN0310VIS-XGW20-532
Spectral Range	532nm
Min focus	2 μ m
Max focus	250 μ m
Magnification	20x
Detection precision	\pm 0.5 μ m
Exposure Time	0.05ms~500ms
Maximum Power	5W
Attenuator	general band: OD1/OD2/OD3/OD4
Communication Interface	USB3.0
External Triggering	Available
Incoming light direction	Vertical (horizontal optional)
Defocusing range	-1mm, +1.3mm
Weight	<1.5Kg
Warranty	1 year

CN0310VIS-XGW20-532

