

**EO-LS-1030/2mJ/2W**

## LD PUMPED ALL-SOLID-STATE EOM Q-SWITCHED LASER AT 1030 nm

All solid state EOM Q-switched laser at 1030 nm has the features of high peak power, high repetition rate, and short pulse duration, which is widely used in marking, carving, measure, research and so on.




### SPECIFICATIONS

|   |  |
|---|--|
| Wavelength (nm)                         | 1030±1   |
| Operating mode                          | Electro-optic Q-switched   |
| Average power (W)                       | 2W (2W@1kHz)<br>Average power (W) = Single pulse energy (mJ) * Rep. rate (kHz) |
| Single pulse energy (mJ)                | 2mJ(2mJ @1kHz)   |
| Rep. rate (kHz)                         | 1  |
| Pulse duration (ns)                     | <20@1kHz   |
| Peak power (MW)                         | 0.1 (0.1MW@1kHz)   |
| Ave power stability (over 4 hours)      | <3%, <5%   |
| Warm-up time (minutes)                  | <10  |
| Beam divergence, full angle (mrad)      | <1   |
| Beam diameter at the aperture (1/e2,mm) | ~2   |
| M <sup>2</sup> factor                   | <1.3   |
| Beam height from base plate (mm)        | 78   |
| Cooled method                           | Air cooled   |
| Operating temperature (°C)              | 10~35  |
| Power supply (220/110VAC)               | PSU-AOM(3U)  |
| Expected lifetime (hours)               | 10000  |
| Warranty period                         | 1 year   |




**EO-LS-1030**



320 (L)×188 (W) ×114(H) mm<sup>3</sup>, 小于15kg

**PSU-AOM (3U)**



483.5 (L) ×454 (W) ×147.5 (H) mm<sup>3</sup>, 8.3 kg