

DATA SHEET

**EO-XS-447**/1~60μJ/1~600mW

## LD PUMPED ALL-SOLID-STATE **EOM Q-SWITCHED LASER** AT 447 nm

All solid state EOM Q-switched laser at 447 nm has the features of high peak power, high repetition rate, and short pulse duration, which is widely used in marking, carving, measure, research and so on.









## SPECIFICATIONS

447±1
Electro-optic Q-switched
1~600mW (600mW@10kHz)
Average power (W) = Single pulse energy (mJ) * Rep. rate (kHz)
1~60(60µJ @10kHz)
10
~4@10kHz
1~15 (15kW@10kHz)
<3%, <5%
<10
<3
~1.5
<2
79
Air cooled
10~35
PSU-AOM (3U)
10000
1 year





