



FC-W-638/ 525/ 450/ 808/ 1550C 66W


HIGH POWER FIBER COUPLING DIODE LASER SYSTEM AT 638/ 525/ 450/ 808/ 1550nm

The FC-W-638/ 525/ 450/ 808/ 1550 series (Fiber Coupling Laser System) have integrated laser diode, fiber coupling optics, laser power supply, LD current and temperature control in ONE box. Its compact dimension and convenient functions, such as power adjustment, temperature control, LED display etc, make it very suitable for scientific research, industrial and medical




SPECIFICATIONS

Wavelength (nm)	638±10	525±10	450±10	808±10	1550±10
Output power (W) @ after 200um fiber	0.4	3.9	4	33	25
Operating mode	CW				
Cooled method	Air cooled				
Fiber Core Diameter (um)	200, 400				
Fiber Connector	SMA905/ FC				
Numerical Aperture (NA)	0.22				
Power stability (rms, over 4 hours)	<1%				
Warm-up time (minutes)	<5				
Operating temperature (°C)	25+/- 3				
Power supply	100-240VAC				
Modulation option	TTL/ Analog 1Hz-1KHz, 1KHz-10KHz, 10KHz-30KHz				
Expected lifetime (hours)	10000				



Laser



430 (L)×220 (W)×120.5 (H)mm³