



**FL-1080-Pico/10~5000mW**

**PICOSECOND ALL FIBER PULSED LASER**

Picosecond all fiber pulsed laser at 1080nm is made features of high output power stability, good beam profile, ultra compact, long lifetime, cost-effectiveness and easy operating, which is widely used in laser radar, precision marking, precision drilling, life science, precision etching, microelectronics, scientific research, etc.




**SPECIFICATIONS**

Wavelength (nm)	1080±1		
Operating mode	Pulsed		
Output power (mW)	10~100	100~2000	2000~5000
Power stability (rms, over 4 hours)	<2%, <3%		
Pulse width (ps) <sup>(1)</sup>	One fixed value between 100~900ps		
M <sup>2</sup> factor	<1.2	<1.8	
Repetition frequency (MHz) <sup>(2)</sup>	One fixed value between 0.1-20MHz		
Polarization ratio	Random / > 15dB		
Warm-up time (minutes)	<15		
Delivery cable length (m)	variable		
Operating temperature (°C)	15~35		
Power supply	24V DC		
Expected lifetime (hours)	10000		
Warranty	1 year		
Options	(1) Pulse width 100~900ps variable (2) Repetition rate 0.1-20MHz variable RS 232 interface Higher output power can be customized		



**FL-1080-Pico**



**344(L)×200(W)×100(H) mm<sup>3</sup> 6.5kg**

