



FL-515-Pico/1mW~1000mW


PICOSECOND ALL FIBER PULSED LASER

Picosecond all fiber pulsed laser at 515nm is made features of high output power stability, good beam profile, ultra compact, long lifetime, cost-effectiveness and easy operating, which is widely used in TCSPC, picosecond processing, laser drilling, glass engraving, scientific research, etc.



SPECIFICATIONS

Wavelength (nm)	515±1	
Operating mode	Pulsed	
Output power (mW)	1~100	100~1000
Power stability (rms, over 4 hours)	<2%, <3%, <5%	
Pulse width (ps) ⁽¹⁾	One fixed value between 100~900 ps	
M ² factor	<1.5	<2
Repetition frequency (MHz) ⁽²⁾	One fixed value between 0.1~20MHz	One fixed value between 0.1~1MHz
Polarization ratio	> 15dB	
Warm-up time (minutes)	<15	
Beam height from base plate (mm)	30	
Delivery cable length (m)	variable	
Operating temperature (°C)	15~35	
Power supply	24V DC	
Expected lifetime (hours)	10000	
Warranty	1 year	
Options	(1) Pulse width 100~900ps variable (2) Repetition rate 0.1~20MHz or 0.1~1MHz variable RS 232 interface Higher output power can be customized	



FL-1030-Pico	Second harmonic	FL-515-Pico
<p style="text-align: center;">344(L)×200(W)×100(H) mm³ 6.5kg</p>	<p style="text-align: center;">220(L)×100(W)×53(H) mm³ 1.1kg</p>	<p style="text-align: center;"> Second harmonic FL-1030-Pico </p>