



LDM-450-6

Typical Device Performance (20°C)

Optical	Unit	Typical Value
CW Output Power	W	6
Center Wavelength	nm	450±10
Electrical		
Threshold Current	A	0.2
Operating Current	A	1.6
Operating Voltage	V	20
TEC		
Operating Voltage Max	V	19.6
Operating Current Max	A	6.0
Fiber*		
Fiber Core Diameter	μm	105
Fiber Cladding Diameter	μm	125
Fiber Buffer Diameter	μm	250
Numerical Aperture	-	0.22
Fiber Length	m	1.0

* Customized fiber and connector available.


Absolute Ratings

	Unit	Min	Max
Operating Temperature	°C	10	40
Operating Relative Humidity	%	-	75
Storage Temperature	°C	-20	80
Storage Relative Humidity	%	-	90
Lead Soldering Temperature, 10 s max	°C	-	250

Addr: No.888 Jinhu Road High-tech Zone, Changchun 130103, P.R.China

Contact: sales@cnilaser.com International Tel: +86-431-85603799 Fax: +86-431-87020258

Package Dimensions (mm)



Pin	Function	Pin	Function
1	LD (+)	5	PD(P)
2	LD (-)	6	Thermistor
3	TEC (-)	7	Thermistor
4	PD(N)	8	TEC (+)



Addr: No.888 Jinhua Road High-tech Zone, Changchun 130103, P.R.China

Contact: sales@cnilaser.com International Tel: +86-431-85603799 Fax: +86-431-87020258