

MDL-D-460/462/465-OEM/4-6W




**OEM BLUE DIODE LASER  
AT 460/462/465nm**

It features ultra compact design, long lifetime, cost-effectiveness and easy operation. They are widely used in laser projection, stage lighting, biomedical applications, metrology, etc.



SPECIFICATIONS

Central wavelength (nm)	460±5/ 462±5/ 465±5
Operating mode	CW
Output power (mW)	>4000, 5000, 6000
Power stability (rms, over 4 hours) at 25°C	<1%, <2%, <3%
Polarization direction	Horizontal+ Vertical
Beam diameter at the aperture (mm)	~3.2×3.2
Beam divergence, full angle (mrad)	~1.4×0.2
Warm-up time (minutes)	<5
Beam height from base plate (mm)	35
Operating temperature (°C)	25+/-3
Driver (12VDC 15A)	PSU-PN7-OEM/ PSU-PN7-OEM-H
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz optional
Expected lifetime (hours)	10000
Warranty	1 year



MDL-D-460/462/465-OEM	PSU-PN7-OEM	PSU-PN7-OEM-H	Accessory (Power supply 100-240VAC)
<p>141(L)×107(W)×56.5(H)mm<sup>3</sup>, 2.2kg</p>	<p>120(L)×65(W)×29(H) mm<sup>3</sup>, 0.3kg</p>	<p>140(L)×80(W)×67(H) mm<sup>3</sup>, 0.6 kg</p>	<p>177.5(L)×62(W)×30(H) mm<sup>3</sup>, 0.5 kg</p>