



MDL-D-635/1200-2000mW



**RED DIODE LASER
AT 635nm**

It features ultra compact design, long lifetime, cost-effectiveness and easy operation. They are widely used in measurement, spectrum analysis, laser lighting show, etc.



SPECIFICATIONS

Central wavelength (nm)	635±10
Operating mode	CW
Output power (mW)	>1200, 1300, ..., 2000
Power stability (rms, over 4 hours)	<1%, <2%, <3%
Polarization direction	Horizontal+ Vertical
Beam diameter at the aperture (mm)	~7.0×4.5
Beam divergence, full angle (mrad)	<2.5×1.0
Warm-up time (minutes)	<5
Operating temperature (°C)	10~35
Power supply (100-240VAC)	PSU-N-LED/ PSU-N-FDA
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz, 1kHz-10kHz, 10kHz-30kHz optional
Expected lifetime (hours)	10000
Warranty	1 year



MDL-D-635	PSU-N-LED	PSU-N-FDA
<p>178(L)×115(W)×90.2(H) mm³, 3.2kg</p>	<p>307(L)×150(W)×106(H) mm³, 3.0kg</p>	<p>307(L)×150(W)×106(H) mm³, 3.0kg</p>