



MDL-HD-650/655-OEM/1800-3000mW




OEM RED DIODE LASER
AT 650/655nm

It features ultra compact design, long lifetime, cost-effectiveness and easy operation. They are widely used in measurement, spectrum analysis, laser lighting show, etc.



SPECIFICATIONS

Central wavelength (nm)	650±10/ 655±10
Operating mode	CW
Output power (mW)	>1800, 1900, ...,3000
Power stability (rms, over 4 hours)	<1%, <2%, <3%
Polarization direction	Horizontal+ Vertical
Beam diameter at the aperture (mm)	~6×8
Beam divergence, full angle (mrad)	~4×3
Warm-up time (minutes)	<5
Beam height from base plate (mm)	35
Operating temperature (°C)	25+/-3
Driver (12VDC 15A)	PSU-6R-OEM/ PSU-6R-OEM-H
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz optional
Expected lifetime (hours)	10000
Warranty	1 year



MDL-HD-650/655-OEM	PSU-6R-OEM	PSU-6R-OEM-H	Accessory (Power supply 100-240VAC)
<p>150(L)×114(W)×60(H) mm³, 3.0kg</p>	<p>110(L)×62(W)×31(H) mm³, 0.2kg</p>	<p>108(L)×83(W)×66(H) mm³, 0.5kg</p>	<p>177.5(L)×62(W)×30(H) mm³, 0.5kg</p>