



MDL-III-1550L/1~50mW



INFRARED DIODE LASER  
AT 1550nm

It features ultra compact design, long lifetime, cost-effectiveness and easy operation. They are used in measurement, communication, spectrum analysis, etc.



SPECIFICATIONS

Central wavelength (nm)	1550±10	1550±5
Operating mode	CW	
Output power (mW)	>1, 2, 3,..., 10	>10, 15,..., 50
Power stability (rms, over 4 hours)	<3%, <2%, <1%	
Transverse mode	Near TEM <sub>00</sub>	
Dimensions of beam at the aperture (1/e <sup>2</sup> ,mm)	~1.5	~5.0
Beam divergence, full angle (mrad)	<3.0	<1.0
Warm-up time (minutes)	<5	
Beam height from base plate (mm)	24.8	
Operating temperature (°C)	10~35	
Power supply	85-264VAC	PSU-III-LED/ PSU-III-FDA (Frequency for 1Hz-30kHz)
	100-240VAC	PSU-A-D (Frequency for 30kHz -100kHz)
Modulation optional	TTL on/off, 1Hz-1kHz, 1kHz-10kHz, 10kHz-30kHz, 30kHz-100kHz; and Analog modulation optional	
Expected lifetime (hours)	10000	
Warranty	1 year	



MDL-III-1550L	PSU-III-LED	PSU-III-FDA	PSU-A-D
<p>143.5(L)×73(W)×46.2(H) mm<sup>3</sup>, 0.7kg</p>	<p>188.6 (L) ×155(W) ×92 (H) mm<sup>3</sup>, 1.5kg</p>	<p>171(L) ×130(W) ×62.2 (H) mm<sup>3</sup>, 1.2kg</p>	<p>162(L) ×144(W) ×70 (H) mm<sup>3</sup>, 1.0kg</p>