

MIL-H-1319/600~1500mW







**LD PUMPED ALL-SOLID-STATE  
INFRARED LASER AT 1319 nm**

All solid state infrared laser at 1319nm is made features of ultra compact, long lifetime, low cost and easy operating, which is used in scientific experiment, optical instrument, optical sensor, measurement, communication, spectrum analysis, etc.

SPECIFICATIONS

Wavelength (nm)	1319±1	
Output power (mW)	>600, 700, 800, ... ,1000	>1000, ... , 1500
Power stability (rms, over 4 hours)	<1%, <2%, <3%, <5%	<2%, <3%, <5%
Transverse mode	Near TEM <sub>00</sub>	
Operating mode	CW	
Warm-up time (minutes)	<10	
M <sup>2</sup> factor	<2. 0	
Beam divergence, full angle (mrad)	<2. 0	
Beam diameter at the aperture (mm)	~3. 0	
Beam height from base plate (mm)	29	
Polarization ratio	>100:1 Horizontal±5 degree (Vertical Optional)	
Pointing stability after warm-up (mrad)	<0.05	
Operating temperature (°C)	10~35	
Power supply (90-264VAC)	PSU-H-LED/PSU-H-FDA/PSU-H-OEM	
Modulation option	TTL on/off, 1Hz-1KHz, 1KHz-10KHz, 10KHz-30KHz; and Analog modulation option	
Expected lifetime (hours)	10000	
Warranty period	1 year	



MIL-H-1319	PSU-H-LED	PSU-H-FDA	PSU-H-OEM
 <p>154.5(L)×77(W)×60(H) mm<sup>3</sup>, 0.9 kg</p>	 <p>277 (L) ×145(W) ×106 (H) mm<sup>3</sup>, 2.6 kg</p>	 <p>275(L) ×145(W) ×104(H) mm<sup>3</sup>, 2.3 kg</p>	 <p>245.5 (L) ×146(W) ×94 (H) mm<sup>3</sup>, 2.2 kg</p>