



MIL-III-946/1~300mW




### LD PUMPED ALL-SOLID-STATE INFRARED LASER AT 946nm

All solid state infrared laser at 946nm is made features of ultra compact, long lifetime, low cost and easy operating, which is used in scientific experiment, measurement, optical instrument, optical sensor, communication, spectrum analysis, etc.



#### SPECIFICATIONS

Wavelength (nm)	946±1	
Output power (mW)	>1, 5, 10, 20, ... , 200	>200, ... , 300
Power stability (rms, over 4 hours)	<1%, <2%, <3%, <5%	<2%, <3%, <5%
Transverse mode	TEM <sub>00</sub>	
Operating mode	CW	
Warm-up time (minutes)	<10	
M <sup>2</sup> factor	<1.5	
Beam divergence, full angle (mrad)	<1.5	
Beam diameter at 1/e <sup>2</sup> (mm)	~1.5	
Beam height from base plate (mm)	24.8	
Pointing stability after warm-up (mrad)	<0.05	
Operating temperature (°C)	10~35	
Power supply (90-264VAC or 5VDC)	PSU-III-LED/PSU-III-FDA/PSU-III-OEM-97	
Expected lifetime (hours)	10000	
Warranty	1 year	



MIL-III-946	PSU-III-LED	PSU-III-FDA	PSU-III-OEM-97
<p>140.5 (L) × 73 (W) × 46.2 (H) mm<sup>3</sup>, 0.6kg</p>	<p>188 (L) × 155(W) × 92 (H) mm<sup>3</sup>, 1.5kg</p>	<p>171 (L) × 130(W) × 62.2 (H) mm<sup>3</sup>, 1.2kg</p>	<p>94(L) × 75(W) × 49(H) mm<sup>3</sup>, 0.23kg</p>