



MLL-III-785/1~2500mW



**LOW NOISE INFRARED DIODE
LASER AT 785nm**

It features ultra compact design, long lifetime, cost-effectiveness and easy operation. They are used in measurement, communication, spectrum analysis, etc.



SPECIFICATIONS

Central wavelength (nm)	785±10	
Operating mode	CW	
Output power (mW)	>1, 50, 100, ... , 2500	
Power stability (rms, over 4 hours)	<3%, <2%, <1%, <0.5%	
Transverse mode	Multimode	
Noise of amplitude(rms, 1Hz~20MHz)	<1%	
Dimensions of beam at the aperture (mm)	~5×8	
Beam divergence, full angle (mrad)	<3.0	
Warm-up time (minutes)	<5	
Beam height from base plate (mm)	24.8	
Operating temperature (°C)	10~35	
Power supply	85-264VAC	PSU-III-LED/ PSU-III-FDA (Frequency for 1Hz-30kHz)
	100-240VAC	PSU-A-D (Frequency for 30kHz -100kHz)
Modulation optional	TTL on/off, 1Hz-1kHz, 1kHz-10kHz, 10kHz-30kHz, 30kHz-100kHz; and Analog modulation optional	
Expected lifetime (hours)	10000	
Warranty	1 year	



MLL-III-785	PSU-III-LED	PSU-III-FDA	PSU-A-D
<p style="text-align: center;">146 (L) × 73 (W) × 46.2 (H) mm³, 0.7kg</p>	<p style="text-align: center;">188.6 (L) × 155 (W) × 92 (H) mm³, 1.5kg</p>	<p style="text-align: center;">171 (L) × 130 (W) × 62.2 (H) mm³, 1.2kg</p>	<p style="text-align: center;">162 (L) × 144 (W) × 70 (H) mm³, 1.0kg</p>