





LASER HEAD <sup>2</sup>	HEATSINK (optional TC-04-FS)	POWER SUPPLY (100-240VAC) optional
<p style="text-align: center;">70(L) × 40(W) × 38(H) mm<sup>3</sup></p>	<p style="text-align: center;">188(L) × 76.2(W) × 43(H) mm<sup>3</sup>, 0.65kg</p>	<p style="text-align: center;">145(L) × 60(W) × 32(H) mm<sup>3</sup></p>

1. Any power level can be selected in this range.
2. The laser head needs to be used on a heat sink with good heat dissipation.