

MPL-H-1053/30~50uJ/300~450mW




LD PUMPED ALL-SOLID-STATE Q-SWITCHED LASER



All solid state Q-switched laser at 1053 nm has the features of high peak power, high repetition rate, and short pulse duration, which is widely used in industry (marking on the diamond or stone), teaching of nonlinear optics, fiber communication, etc.



SPECIFICATIONS

Central wavelength (nm)		1053 ± 1
Operating mode		Q-switched pulsed laser
Single pulse energy (μJ)		30~50
Pulse duration (ns)		~10
Peak power (W)		3000~5000
Rep. rate (kHz)	FIXED	Setting up one fixed rep. rate internal between 1Hz-4kHz with stable pulse energy, pulse duration and pulse period.
	EXT TRIG	1Hz-4kHz by external trigger with stable pulse energy, pulse duration and pulse period.
	QCW	QCW state with one rep. rate between 5kHz-30kHz.
Average power (mW)		Average power (mW) = Single pulse energy (μJ) * Rep. rate (kHz)
Ave power stability (over 4 hours)		<1%, <2%, <3%, <5%
Transverse mode		Near TEM ₀₀
Warm-up time (minutes)		<10
M ² factor		<1.5
Beam divergence, full angle (mrad)		<2.0
Beam diameter at the aperture (mm)		~3.0
Beam height from base plate (mm)		29
Operating temperature (°C)		10~35
Power supply (90-264VAC)		PSU-H-FDA
Expected lifetime (hours)		10000
Warranty		1 year



<p style="text-align: center;">MPL-H-1053</p>  <p style="text-align: center;">154.5(L)×77(W)×60(H) mm³, 0.9 kg</p>	<p style="text-align: center;">PSU-H-FDA</p>  <p style="text-align: center;">275(L)×145(W)×104(H) mm³, 2.3 kg</p>
---	--