



MRL-III-671/1~200mW



**LD PUMPED ALL-SOLID-STATE  
RED LASER AT 671nm**

All solid state 671nm red laser is made features of ultra compact, long lifetime, low cost and easy operating, which is widely used in measurement, spectrum analysis, and laser lighting show, etc.



SPECIFICATIONS

Wavelength (nm)	671 ± 1	
Operating mode	CW	
Output power (mW)	>1, 5, 10, 20, ... , 100	>100, ... , 200
Power stability (rms, over 4 hours)	<1%, <2%, <3%,	<2%, <3%,
Transverse mode	TEM <sub>00</sub>	
Warm-up time (minutes)	<10	
M <sup>2</sup> factor	<1.2 (<1.1 optional)	<1.2
Beam divergence, full angle (mrad)	<1.5	
Beam diameter at 1/e <sup>2</sup> (mm)	~1.2	
Beam height from base plate (mm)	24.8	
Polarization ratio	>100:1 (0 or 90 degree)	
Pointing stability after warm-up (mrad)	<0.05	
Operating temperature (°C)	10~35	
Power supply (90-264VAC or 5VDC)	PSU-III-LED/PSU-III-FDA/PSU-III-OEM-97	
Modulation option	TTL on/off, 1Hz-1KHz, 1KHz-10KHz, 10KHz-30KHz; and Analog modulation option	
Expected lifetime (hours)	10000	
Warranty	1 year	



MRL-III-671	PSU-III-LED	PSU-III-FDA	PSU-III-OEM-97
<p>140.5 (L) × 73 (W) × 46.2 (H) mm<sup>3</sup>, 0.6kg</p>	<p>188 (L) × 155(W) × 92 (H) mm<sup>3</sup>, 1.5kg</p>	<p>171 (L) × 130(W) × 62.2 (H) mm<sup>3</sup>, 1.2kg</p>	<p>94(L) × 75(W) × 49(H) mm<sup>3</sup>, 0.23kg</p>