



中国长春新产业光电技术有限公司
Changchun New Industries Optoelectronics Tech. Co., Ltd

PGL-VI-705



Diode laser at 705nm is made features of ultra compact, long lifetime, low cost and easy operating, which made it be used widely in measurement, spectrum analysis and laser show, etc.

SYSTEM SPECIFICATIONS*

Wavelength	nm	705
Wavelength tolerance	nm	±10
Output power	mW	1-20
Operating mode		CW
Transverse mode		Near TEM ₀₀
Beam diameter at the aperture(1/e ²)	mm	~3.5
Beam divergence, full angle	mrad	<1
Expected lifetime	hours	10,000
Warranty	months	6

Focus adjustable laser is optional.

ELECTRICAL SPECIFICATIONS

Operating voltage(internal PCB)	3VDC(TTL10kHz)
Operating voltage(external PCB1)	5VDC(TTL30kHz or Analog0-3V,0-5V)
Operating voltage(external PCB2)	5-12VDC(TTL30kHz and Analog 0-3V,0-5V)
Connection	Cable with flying leads

ENVIRONMENTAL CONDITIONS

Operating temperature	0°C to 40°C
Storage temperature	-20°C to 80°C
Humidity	< 90 %, non-condensing
Dissipated heat	< 1W

MECHANICAL SPECIFICATIONS


Diameter head Φ	mm	12
Length	mm	50
Material		Aluminum
Shell polarity		The housing has non-polarity.

*All testing data under the conditions of temperature 25°C.




中国长春新产业光电技术有限公司
Changchun New Industries Optoelectronics Tech. Co., Ltd

Dimensions of laser (Internal PCB, $\Phi 12 \times 50 \text{mm}^2$, 3VDC, TTL)



Dimensions of external PCB1 ($11 \times 25 \text{mm}^2$, 5VDC, TTL or Analog)



Dimensions of external PCB2 (*wide voltage input range*, $20 \times 30 \text{mm}^2$, 5-12VDC, TTL and Analog)

