



Advantage:

- ◆ Precise temperature control, stepless adjustment
- ◆ Good gas uniformity index inside the box
- ◆ Low temperature overcharge
- ◆ Far beyond control
- ◆ Long average time between failures

Model	PTN4002-M
Internal volume	216L
Temperature range	RT+20°C~+300°C
Temperature fluctuation	±0.5°C
Temperature deviation	±3°C
Heating time	≤40min
Loading weight	Empty
Outer material	Galvanized Steel Sheet with Powder coated
Inner material	Stainless steel
Insulation material	Rock wool
Controller	FUJI
Running mode	Manual or program eunning
Control mode	PID
Fill gas	N ₂
Fill gas(N ₂) flow	20~100L/min(Adjustable manully)
Communication	RS485 connector,modbus communication protocol(optional)
Inner size	600×600×600mm
Outer size	885×1280×1090mm
Installing power	6KW
Power of constant temperature	1KW
Power supply temperature	AC380V±10% 50Hz, 3Phase5Wires
Weight	280kg
Accessories	1 pc of Manua,2 pcs of Shelves
Standards and regulations	GB/T11158、GB/T2423.2、GB/T5170.2