



Advantage:

- ◆ Precise temperature control and stepless adjustment
- ◆ Wide temperature range
- ◆ Fast temperature rise and fall speed
- ◆ Fast linear temperature rise and fall rate
- ◆ Large capacity storage space
- ◆ Long-life

Model	PTR702W-T0404	PHR702W-T0404
Internal volume	225L	
Temperature range	-70°C~+180°C	
Temperature fluctuation	±0.5°C	
Temperature uniformity	≤2°C	
Temperature deviation	±2°C	
Humidity range	/	20%~98%R.H.
Humidity deviation	/	+2%~3%R.H.(≥75%R.H.) ±5%R.H.(< 75%R.H.)
Temperature changing rate	5°C/min	
Loading weight	Empty	
Outer material	Galvanized Steel Sheet with Powder coated	
Inner material	SUS304	
Insulation material	Rock wool	
Refrigeration	Cascade refrigeration	
Refrigerant	R404A/R23	
Heater	Nichrome alloy heater	
Viewing window	400×550mm	
Temperature sensor	Pt100	
Testing port	Ø100,2 pcs on both sides	
Controller	Siemens Smart PLC,Proface touch Panel	
Recorder	U-Disk	
Communication	LAN,Remote Controlling Soft(Optional)	
Inner size	500×600×750mm	
Outer size	1600×900×1900mm	
Maximum power	10KW	
Maximum current	18A	
Power supply	AC380V±10% 50Hz, 3Phase5Wires	
Accessoriesman	1 pc of Manua,2 pcs of Shelves,2 pcs of Plugs	
Standards and regulations	GB/T10592、GB/T2423.22、GB/T10589、GB/T5170.2、IEC60068-3-5	