



Beam Profiler



Features:

Spectral range:248-266nm

Beam diameter:5 μ m~500 μ m

Maximum power to 2W

PC software

SPECIFICATIONS:

Product Name	CD0307U-XD-266
Spectral Range	248nm-266nm
Min focus	5 μ m
Max focus	500 μ m
Pixel Size	3.45 μ m
Resolution	2448x2048
Full Resolution Frame Rate	5-10fps
Dynamic Range	70dB
Magnification	10x
Detection precision	$\pm 1 \mu$ m
Exposure Time	0.05ms~500ms
Maximum Power	2W
Attenuator	general band: OD1/OD2/OD3/OD4 (248-266nm)
Communication Interface	USB3.0
External Triggering	Available
Weight	<1.5Kg
Incoming light direction	Vertical (horizontal optional)
Defocusing range	-1mm, +1.3mm
Warranty	1 year

CD0307U-XD-266

