

## 长春新产业光电技术有限公司

Changchun New Industries Optoelectronics Tech, Co., Ltd,

DATA SHEET

FC-W-1270H/5~30W

## HIGH POWER FIBER COUPLING DIODE LASER SYSTEM AT 1270 nm

**SPECIFICATIONS** 

The FC-W-1270H series (Fiber Coupling Laser System) have integrated laser diode, fiber coupling optics, laser power supply, LD current and temperature control in ONE box. Its compact dimension and convenient functions, such as power adjustment, temperature control, LED display etc, make it very suitable for pumping, scientific research, industrial and medical applications.



Model	FC-W-1270H
Wavelength (nm)	1270±10
Operating mode	CW
After fiber output power (W)	>5, 10,, 30
Power stability (rms, over 4 hours)	<2%, <1%, <0.5%
Red pilot light	Available on request
Fiber core diameter (µm)	400/600
Fiber NA	0.22
Fiber connector	SMA905
Fiber length (m)	2
LED display	Diode current
Operating temperature (°C)	10~40
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz optional
Input power	100-240VAC, 50 to 60 Hz
Cooling Way	Air Cooled
Dimensions(mm <sup>3</sup> )	370 (L) ×406 (W) ×188 (H)
Expected lifetime (hours)	10000
Warranty	1 year





668 Chuangxin Road High-tech Zone Changchun, China

Warranty
I year

FC-W-1270H

Image: Constraint of the state of t