



MDL-III-1030/1~500mW




INFRARED DIODE LASER  
AT 1030nm

It features ultra compact design, long lifetime, cost-effectiveness and easy operation. They are widely used in measurement, spectrum analysis, etc.



SPECIFICATIONS

Central wavelength (nm)	1030±1	
Operating mode	CW	
Output power (mW)	>1, 100, 200, ..., 500	
Power stability (rms, over 4 hours)	<3%, <2%, <1%, <0.5%	
Transverse mode	TEM <sub>00</sub>	
Ellipticity	>0.95	
M <sup>2</sup> factor	<1.1	
Dimensions of beam at the aperture (mm)	~1.0	
Beam divergence, full angle (mrad)	~1.5	
Warm-up time (minutes)	<5	
Beam height from base plate (mm)	24.8	
Operating temperature (°C)	10~35	
Power supply	85-264VAC	PSU-III-LED/ PSU-III-FDA (Frequency for 1Hz-30kHz)
	100-240VAC	PSU-A-D (Frequency for 30kHz -100kHz)
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz, 30kHz-100kHz optional	
Expected lifetime (hours)	10000	
Warranty	1 year	



MDL-III-1030	PSU-III-LED	PSU-III-FDA	PSU-A-D
<p>146 (L) × 73 (W) × 46.2 (H) mm<sup>3</sup>, 0.7kg</p>	<p>188.6 (L) × 155 (W) × 92 (H) mm<sup>3</sup>, 1.5kg</p>	<p>171 (L) × 130 (W) × 62.2 (H) mm<sup>3</sup>, 1.2kg</p>	<p>162 (L) × 144 (W) × 70 (H) mm<sup>3</sup>, 1.0kg</p>