


MDL-MD-460/462/465/1-6000mW




BLUE DIODE LASER AT 460/462/465nm

It features ultra compact design, long lifetime, cost-effectiveness and easy operation. They are widely used in laser projection, laser shows, biomedical applications, holography, metrology. etc.




SPECIFICATIONS

Central wavelength (nm)	460±10/ 462±10/ 465±10	
Operating mode	CW	
Output power (mW) ¹	1-6000	
Power stability (rms, 4 hours ± 3°C)	<2%, <1%, <0.5%	
Transverse mode	Multimode	
Polarization direction	Horizontal+ Vertical	Horizontal/ Vertical
Beam diameter at the aperture (mm)	~1.0×2.5	~2.0×2.5
Beam divergence, full angle (mrad)	~3.4×3.8	~3.3×3.8
Warm-up time (minutes)	<5	
Beam height from base plate (mm)	25	
Operating temperature (°C)	25±3	
Power supply (100-240VAC)	PSU-H-FDA/PSU-H-LED/PSU-N-LED	
Modulation option	DC-1kHz, 1kHz-10kHz, 10kHz-30kHz optional; TTL and Analog optional	
Expected lifetime (hours)	>10000	




LASER HEAD²






129 (L) × 70 (W) × 45 (H) mm³, 0.7kg

HEATSINK (TC-04)



188 (L) × 76.2 (W) × 43 (H) mm³, 0.65kg

POWER SUPPLY (PSU-H-FDA) ³	POWER SUPPLY (PSU-H-LED) ⁴	POWER SUPPLY (PSU-N-LED) ⁴
 275 (L) × 145 (W) × 104 (H) mm³, 2.1kg	 277 (L) × 145 (W) × 106 (H) mm³, 2.3kg	 283 (L) × 180 (W) × 104 (H) mm³, 2.5kg

1 Any power level can be selected in this range.

2 The laser head needs to be used on a heat sink with good heat dissipation.

3 Fixed output power; Modulation up to 30kHz.

4 Output power adjustable 10-100%; RS232 control optional; Modulation up to 30kHz.