



MGL-FN series (551-570nm)








LD PUMPED ALL-SOLID-STATE LASER

The all-solid-state laser features high output power stability, a good beam profile, an ultra-compact design, a long lifetime and ease of operation. It is widely used in collimation, laser medical treatment, scientific experiments, optical instruments, and more.



SPECIFICATIONS

Wavelength (nm)	552±1	555±1	556±1		561±1	
Operating mode	CW					
Output power (mW) ¹	1-300	1-100	200-500	500-800	300-500	500-1000
Power stability (rms, 4 hours ±3°C)	<3%, <2%, <1%			<5%, <3%, <2%	<3%, <2%, <1%	<5%, <3%, <2%
Transverse mode	TEM ₀₀					
M ²	<1.5			<1.2	<1.5	
Beam diameter at the aperture (1/e ² , mm)	<2.0	<1.5		<2.0		
Beam divergence (mrad)	<1.5					
Polarization ratio	>100:1, Vertical (Horizontal optional)					
Warm-up time (minutes)	<5					
Pointing stability (μrad) (over 2 hours after warm-up and ±3°C)	<50					
Pointing stability over temperature (μrad/°C)	<8					
Beam height from base plate (mm)	27.4					
Operating temperature (°C)	10-35					
Modulation optional	DC-1kHz, 1kHz-10kHz, 10kHz-30kHz optional; TTL and Analog optional					
Power supply (100-240VAC)	PSU-H-FDA/PSU-H-LED/PSU-SR					
Expected lifetime (hours)	>10000					

LASER HEAD ²	HEATSINK (optional TC-02-FS)	POWER SUPPLY (PSU-H-FDA) ³
 197(L)×70(W)×50(H) mm³, 1.5kg	 202(L)×110(W)×47.5(H) mm³, 1.25kg	 276.6(L) ×145(W) ×103.6(H) mm³, 2.3kg
POWER SUPPLY (PSU-H-LED) ⁴	POWER SUPPLY (PSU-SR) ⁴	
 273.6 (L) ×145(W) ×106 (H) mm³, 2.3kg	 188(L) ×145(W) ×83(H) mm³, 1.2kg	

1 Any power level can be selected in this range.

2 The laser head needs to be used on a heat sink with good heat dissipation.

3 Fixed output power.

4 Output power adjustable 10-100%; RS232 control optional.