


MIL-V-1342/1~5W

SPECIFICATIONS

Wavelength (nm)	1342±1
Operating mode	CW
Output power (W)	>1,2,3, ..., 5
Power stability (rms, over 4 hours)	<2%, <1%
Transverse mode	TEM ₀₀
M ² factor	<1.3
Beam divergence, full angle (mrad)	<3.0
Beam diameter at the aperture (1/e ² , mm)	~2.0
Warm-up time (minutes)	<10
Polarization ratio	>50:1(100:1 Optional), Horizontal(Vertical Optional)
Beam height from base plate (mm)	80
Operating temperature (°C)	10~35
Power supply (90-264VAC)	PSU-W-LED
TTL / Analog modulation	TTL or Analog with 1Hz-1kHz 1kHz-10kHz, 10kHz-30kHz optional
Expected lifetime (hours)	10000
Warranty period	1 year




LD PUMPED ALL-SOLID-STATE INFRARED LASER AT 1342nm

All solid state infrared laser at 1342nm is made features of ultra compact, long lifetime and easy operating, which is used in scientific experiment, optical instrument, optical sensor, measurement, communication, spectrum analysis, etc.




MIL-V-1342



335 (L) × 140 (W) × 110 (H) mm³, 6.2 kg

PSU-W-LED



301.5 (L) × 185 (W) × 114 (H) mm³