



MLL-III-975-SM/1-1000mW




LOW NOISE INFRARED DIODE LASER AT 975nm

It features ultra compact design, long lifetime, cost-effectiveness and easy operation. They are used in medical imaging, flow cytometry, DNA sequencing, etc.



SPECIFICATIONS

Central wavelength (nm)	975±5	975±2
Operating mode	CW	
Output power (mW) ¹	1-20	20-1000
Power stability (rms, 4 hours ± 3°C)	<2%, <1%, <0.5%	
Noise of amplitude (rms, 20Hz-20MHz)	<1%, <0.5%	
Fiber type	SM fiber, PM fiber optional	
Fiber Core diameter	4-9μm, 0.12NA	
Fiber connector	FC/PC, FC/APC optional	
Fiber length ²	1m	
Fiber jacket	Metal, PVC optional	
Transverse mode	TEM ₀₀	
Ellipticity	>0.95	
M ² after fiber	~1.1	
Warm-up time (minutes)	<5	
Cooled method	Conduction	
Operating temperature (°C)	10-35	
Power supply (100-240VAC)	PSU-III-FDA/PSU-III-LED/PSU-A-D/PSU-III-OEM	
Modulation option	DC-1kHz, 1kHz-10kHz, 10kHz-30kHz, 30kHz-100kHz optional; TTL and Analog optional	
Expected lifetime (hours)	>10000	



LASER HEAD




126.5 (L) × 73 (W) × 46.2 (H) mm³, 0.7kg

POWER SUPPLY (PSU-III-FDA)³



171 (L) × 130 (W) × 62.2 (H) mm³, 1.2kg

POWER SUPPLY (PSU-III-LED)⁴



179 (L) × 155 (W) × 92 (H) mm³, 1.5kg

POWER SUPPLY (PSU-A-D) ⁵	DRIVER (PSU-III-OEM) ³	POWER SUPPLY (100-240VAC) optional
 144 70 162 162 (L) × 144 (W) × 70 (H) mm³, 1.0kg	 100 55.2 33 7 40*40*10 K向 2 x M3 5 42 62 31 60 100 (L) × 62 (W) × 55.2 (H) mm³, 0.5kg	 31.8 125.7 50.2 125.7 (L) × 50.2 (W) × 31.8 (H) mm³, 0.3kg

1 Any power level can be selected in this range.

2 Other lengths are available on request.

3 Fixed output power; Modulation up to 30kHz.

4 Output power adjustable 10-100%; RS232 control optional; Modulation up to 30kHz.

5 Output power adjustable 10-100%; RS232 control optional; Modulation up to 100kHz.