



MLL-K-457-SM

### SM FIBER OUTPUT LASER

CNI has a long experience in the delivery of fiber coupled laser light sources providing high efficiency and long term stability. All laser types can be offered with appropriate fiber coupling systems. This type is specifically designed for single-mode fiber(include PM) coupling with high power stability and long term stability.




#### SPECIFICATIONS

Part number	MLL-K-457-SM
Wavelength (nm)	457±1
Operating mode	CW
Output power (W) <sup>1</sup>	1-2
Power Stability (rms, 4 hours ± 3°C)	<3%, <2%, (<1% optional)
Transverse mode	TEM <sub>00</sub> (single mode fiber output)
M <sup>2</sup>	<1.1
Polarization (optional)	>50:1 after PM fiber
Fiber core diameter	3.5um,0.10NA
Fiber connector	FC/APC
Fiber length <sup>2</sup>	1m
Fiber Jacket	PVC, Metal optional
Warm-up time (minutes)	<10
Cooled method	Water cooled
Operating temperature (°C)	10-30
Power supply (100-240VAC)	PSU-W-LED
Modulation option	DC-1kHz, 1kHz-10kHz, 10kHz-30kHz optional; TTL and Analog optional
Expected lifetime (hours)	>10000




LASER HEAD




280 (L) × 110 (W) × 96 (H) mm<sup>3</sup>

POWER SUPPLY



301.5 (L) × 185 (W) × 114 (H) mm<sup>3</sup>, 3.0 kg

WATER CHILLER (WCH-580)



369.8 (L) × 258.4 (W) × 240.6 (H) mm<sup>3</sup>, 10.5 kg

1 Any power level can be selected in this range.

2 Other lengths are available on request.