



MRL-FN series (600-650nm)



LD PUMPED ALL-SOLID-STATE LASER






All solid state laser is made features of high output power stability, good beam profile, ultra compact, long lifetime and easy operating, which is widely used in collimation, laser medical treatment, scientific experiment, optical instrument, etc.



SPECIFICATIONS

Part number	MRL-FN-604	MRL-FN-607	MRL-FN-639
Wavelength (nm)	604±1	607±1	639±1
Operating mode	CW		
Output power (mW)	1-100	500-800	800-1800
Power stability (rms, over 4 hours)	<3%, <2%, <1%	<2%, <1%, 0.5%	<2%, <1%, 0.5%
Transverse mode	TEM ₀₀		
M ² factor	<1.2		
Beam diameter at the aperture (1/e ² , mm)	<1.2	<1.5	
Beam divergence, full angle (mrad)	<1.5		
Polarization Ratio	>100:1, Vertical (Horizontal Optional)		>100:1, Horizontal (Vertical Optional)
Warm-up time (minutes)	<5		
Pointing stability after warm-up (mrad)	<0.05		
Beam height from base plate (mm)	27.4		
Operating Temperature (°C)	10-35		
Modulation optional	DC-30kHz; TTL and Analog modulation optional		
Power supply (90-264VAC)	PSU-H-LED/PSU-H-FDA/PSU-SR		
Expected lifetime (hours)	>10000		

Note: The laser head needs to be used on a heat sink with good heat dissipation.

LASER HEAD		HEATSINK(OPTIONAL TC-02-FS)	
 197(L)×70(W)×50(H) mm³, 1.5 kg		 220(L)×110(W)×47.5(H) mm³, 1.25 kg	
POWER SUPPLY (PSU-H-LED)	POWER SUPPLY (PSU-H-FDA)	POWER SUPPLY (PSU-SR)	
 273.6 (L) ×145(W) ×106 (H) mm³, 2.3 kg		 188(L) ×145(W) ×83(H) mm³, 1.2kg	
 276.6(L) ×145(W) ×103.6(H) mm³, 2.3 kg			