

Laser Power Meter



TS2/ TS5/ TS15-USB

Features:

Wavelength range: 0.19 -25 μ m

Power measurement range: 2mW-15W

Single channel/ multi-channel power measurement

PC upper computer software display measurement

SPECIFICATIONS

Model	TS2-USB	TS5-USB	TS15-USB
Power Range	2 mW - 2 W	2 mW - 5 W	2 mW - 15 W
Active Area Diameter	22 mm	22 mm	22 mm
Probe Coating Film	Broadband coating		
Probe Material	Thermopile		
Wavelength Range	0.19-25 μ m		
Max. Average Power Density	15 kW/cm ²		
Max. Energy Density	0.15J/cm ² ,1064nm,1ns		
Sensitivity	2 mW	2 mW	2mW
Measurement Uncertainty	\pm 2%		
Response Time (0-90%)	<1 sec.		
Linearity	\pm 1%		
Resolution	100uW		
Accuracy	< \pm 2%		
Cooling Method	Air cooling		
Computer Interface	USB 1.1 and USB 2.0		
Temperature (Operating)	5°C - 45°C (41°F - 113°F)		
Temperature (Storage)	-20°C - 70°C (-4°F - 158°F)		
Warranty Period	1 year		

TS2/ TS5/ TS15-USB

