

Laser Power Meter



TS100/TS200-USB

Features:

Wavelength range: 0.19 -25 μ m

Power measurement range: 50mW-300W

Single channel/ multi-channel power measurement

PC upper computer software display measurement

SPECIFICATIONS

Model	TS300-USB
Power Range	50mW- 300 W
Active Area Diameter	25 mm
Probe Coating Film	Broadband coating
Probe Material	Thermopile
Wavelength Range	0.19-25 μ m
Max. Average Power Density	45 kW/cm ²
Max. Energy Density	0.3J/cm ² ,1064nm,7ns
Sensitivity	50mW
Measurement Uncertainty	\pm 2%
Response Time (0-90%)	<1 sec.
Linearity	\pm 1%
Resolution	10mW
Accuracy	< \pm 2%
Cooling Method	Fan cooling
Computer Interface	USB 1.1 and USB 2.0
Temperature (Operating)	5°C - 45°C (41°F - 113°F)
Temperature (Storage)	-20°C - 70°C (-4°F - 158°F)
Warranty Period	1 year

TS300-USB

